KERN MAP 80K1



Hand grip dynamometer, e.g. for rehabilitation treatment after accidents



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Hand grip dynamometer
Product family	MAP

Measuring System	
Weighing capacity [Max]	80 kg
Readability [d]	100 g
Units	kg Ib
Recommended adjusting weight	40 kg (M1)
Possible calibration points	40 kg

1 cools to cameration points	10 118
Approval	
7.pp. 37a.	
CE mark	/
	-
Display	

Construction		
Display digit height	12 mm	
Display type	LCD graphic	

Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min

55×102×212 mm

Dimensions device (W×D×H)

Power Supply	
Supplied power supply	Battery
Battery	CR2450

Battery / accumulator type	Li-Metal
Battery capacity	630 mAh
Battery voltage	3 V
Battery operating time	53 h

Environmental conditions	
Use temperature [Min]	5 °C
Use temperature [Max]	35 °C
Humity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Dimensions transport container (W×D×H)	350×265×85 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	367×285×100 mm
Net weight	0,306 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	1,8 kg
Shipping weight	2,1 kg

Services (optional)	
Article number for factory calibration	961-102K

Pictograms

STANDARD



OPTION



1