KERN MBC 20K10EM



Elegantly-shaped baby scale – with approval for professional mobile or stationary medical use in medical diagnostics, verification optional



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Baby scale
Product family	MBC

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	20 kg
Readability [d]	0,01 kg
Resolution	2.000
Linearity	± 0,01 kg
Reproducibility	0,01 kg
Tare range	19,99 kg
Default unit	kg
Units	kg
Minimum weight [Min]	0,2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	20 kg (M1)
Stabilization time	3 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,01 kg

Approval	
CE mark	✓
Pattern approval for conformity assessment	/
Accuracy classe	III
Verification scale interval [e]	0,01 kg
Conformity assessment possible ex works	/
Approval according to 93/42/EEC (med.)	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	200×130×60 mm
Dimension housing (W×D×H)	330×280×72 mm
Dimensions weighing platform (W×D×H)	600×280×55 mm
Dimensions completely mounted (W×D×H)	600×407×120 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	plastic
Dimensions weighing surface (W×D)	600×280 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min 5 min 30 min 15 min
Tare function	manual (single & multi)
Hold function	✓
Function for averaging under unstable weighing conditions	✓

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery
Plug-in power supply / adapter for countries - optional	EURO UK CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	40 h
Battery	6×1.5 V AA

KERN MBC 20K10EM



Elegantly-shaped baby scale - with approval for professional mobile or stationary medical use in medical diagnostics, verification optional

Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery voltage	9 V
Battery operating time	20 h

Environmental conditions	
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	480×650×175 mm
Net weight	4,5 kg
Shipping method	Parcel service
Net weight approx.	4,6 kg
Gross weight approx.	6 kg
Shipping weight	10,9 kg

Services (optional)	
Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-128.
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD







OPTION









FACTORY

