

# KERN MBC-A04

Mains adapter (AUS, CH, EU, K, US)

# KERN

## Pictograms

### STANDARD



### Category

Brand	KERN
Product category	Balance
Product group	Power adapter

### Approval

CE mark	✓
---------	---

### Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH

### Environmental conditions

Storage temperature [Max]	60 °C
---------------------------	-------

### Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	16×5×5 mm
Net weight	0,165 kg
Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,20 kg
Shipping weight	0,198 kg