KERN MPD 250K100M



Professional step-on personal floor scale approved as a medical device, verification optional



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Personal floor scale
Product family	MPD

Measuring System		
Conformity assessment possible	✓	
Construction type of the scale	Single-range balance	
Weighing system	Strain gauge	
Weighing capacity [Max]	250 kg	
Readability [d]	0,1 kg	
Resolution	2.500	
Linearity	± 0,1 kg	
Reproducibility	0,1 kg	
Default unit	kg	
Units	kg	
Minimum weight [Min]	2 kg	
Adjustment options	Adjusting with external weight	
Recommended adjusting weight	200 kg (M1)	
Stabilization time	3 s	
Warm-up time	10 min	
Eccentric loading at 1/3 [Max]	0,1 kg	

Approval	
CE mark	✓
Pattern approval for conformity assessment	1
Accuracy classe	III
Verification scale interval [e]	0,1 kg

Conformity assessment possible ex works	✓
Approval according to 93/42/EEC (med.)	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height	25 mm
Languages of the user interface	Symbol language
Construction	

Construction		
Dimension display device (W×D×H)	200×130×60 mm	
Dimensions weighing platform (W×D×H)	form 365×360×80 mm	
Dimensions completely mounted (W×D×H)	365×490×120 mm	
Material display housing Plastics		
Material housing	steel, lacquered	
Material weighing plate	plastic	
Levelling feet adjustable	✓	

Functions	
Number of keys for operation	1
Auto-off interval(s) in battery mode/rechargeable battery mode	15 sec
Tare function	none

rare randion	Horic
Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h

1

KERN MPD 250K100M



Professional step-on personal floor scale approved as a medical device, verification optional

Rechargeable battery operating time - backlight off

40 h

Battery Battery / accumulator type

Alkali(-Manganese)

Battery connection

Pad + Spring

6×1.5 V AA

Battery operating time

20 h

Environmental conditions

Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force	: [d] (N)	1 d
-------------------	-----------	-----

Dimensions packaging (W×D×H) 560×440×200 mm

Net weight 8,96 kg

Parcel service Shipping method

Net weight approx. 9 kg Gross weight approx. 11 kg

Shipping weight 10,4 kg

Services (optional)

Article number for adjustment at the location of installation

961-249

Article number for conformity assessment

965-129

Article number for DAkkS

conformity (verification)

calibration

963-129

Article number for certificate of

969-517

Pictograms

STANDARD









OPTION





FACTORY

