

# KERN MPE 250K100PM



High quality personal floor scale with BMI function – with approval for professional medical use in medical diagnostics, verification optional



Accuracy classe	III
Verification scale interval [e]	0,1 kg
Conformity assessment possible ex works	✓
Approval according to 93/42/EEC (med.)	✓

<b>Display</b>	
Display type	LCD
Display backlight	✓
Display digit height - smallest digit	2 mm
Display digit height	25 mm
Languages of the user interface	Symbol language

<b>Construction</b>	
Dimension display device (W×D×H)	200×55×128 mm
Dimensions weighing platform (W×D×H)	365×360×80 mm
Dimensions completely mounted (W×D×H)	365×570×1030 mm
Material display housing	Plastics
Material housing	steel, lacquered
Material weighing plate	plastic
Dimensions weighing surface (W×D)	327×333 mm
Transport wheels	✓
Stand height	940 mm

<b>Functions</b>	
Number of keys for operation	7
Auto-off interval(s) in mains power mode	5 min 30 min selectable 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min 5 min 30 min 15 min
PreTare function	✓
Tare function	manual (single & multi)
Hold function	✓
Function for averaging under unstable weighing conditions	✓
Function for BMI calculation	✓
Interfaces	RS-232 standard

<b>Power Supply</b>	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz

<b>Category</b>	
Brand	KERN
Product category	Medical scale
Product group	Personal floor scale
Product family	MPE

<b>Measuring System</b>	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	250 kg
Readability [d]	0,1 kg
Resolution	2.500
Linearity	± 0,1 kg
Reproducibility	0,1 kg
Tare range	-249,9 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 kg (M1)
Stabilization time	3 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,1 kg

<b>Approval</b>	
CE mark	✓
Pattern approval for conformity assessment	✓

# KERN MPE 250K100PM



High quality personal floor scale with BMI function – with approval for professional medical use in medical diagnostics, verification optional

Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	40 h
Battery	6×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Battery insert
Battery operating time	20 h

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	1010×290×445 mm
Net weight	11,26 kg
Shipping method	Parcel service
Net weight approx.	12 kg
Gross weight approx.	14 kg
Shipping weight	26,1 kg

## Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-129
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION



### FACTORY

