# KERN MPS 200K100PM



Stylish personal floor scale with BMI function – with approval for professional medical use in medical diagnostics, verification optional



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Personal floor scale
Product family	MPS

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	200 kg
Readability [d]	0,1 kg
Resolution	2.000
Linearity	± 0,1 kg
Reproducibility	0,1 kg
Default unit	kg
Units	kg
Minimum weight [Min]	2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 kg (M1)
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,1 kg
Measuring range measuring rod (cm)	60-100cm @ 0,1cm ± 0,5cm 100-205cm @ 0,1cm ± 1cm

Approval		
CE mark	✓	
Pattern approval for conformity assessment	✓	
Accuracy classe	III	

Verification scale interval [e]	0,1 kg
Conformity assessment possible ex works	/
Approval according to 93/42/EEC (med.)	✓

Display	
Display type	LCD
Display digit height	27 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	215×110×45 mm
Dimensions weighing platform (W×D×H)	275×295×58 mm
Dimensions completely mounted (W×D×H)	275×445×1020 mm
Material display housing	Plastics
Material housing	steel, lacquered
Material weighing plate	steel, lacquered
Levelling feet adjustable	✓
Stand height	1000 mm

Functions	
Number of keys for operation	20
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 4 min 5 min 2 min
PreTare function	✓
Tare function	manual (multi)
Hold function	✓
Function for averaging under unstable weighing conditions	✓
Function for BMI calculation	✓
Interfaces	RS-232 standard

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH

1

# KERN MPS 200K100PM



Stylish personal floor scale with BMI function – with approval for professional medical use in medical diagnostics, verification optional

Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	14 h
Rechargeable battery operating time - backlight off	35 h
Battery	6×1.5 V AA
Battery operating time	50 h

Environmental conditions	
Humity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	1180×400×330 mm
Net weight	6,6 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	11 kg
Shipping weight	31,2 kg

Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-129
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

## Pictograms

#### **STANDARD**



### OPTION



### **FACTORY**

