KERN MSW 200S05



Convenient circumference measuring tape with practical pull-out mechanism



Category	
Brand	KERN
Product categoriy	Medical scale
Product group	Body size measurement
Product family	MSW
Measuring System	
Default unit	mm
Units	mm
Division	1 mm
Measuring range length [Min]	10 cm
Measuring range length [Max]	2,05 m
Tolerance measuring rod	5 mm
Measuring range measuring rod	0-200cm @ 0,1cm ±
(cm)	0,5cm
Approval	
CE mark	✓
Approval according to 93/42/EEC	1
(med.)	•
Construction	
Dimensions device (W×D×H)	55×90×20 mm
Dimension housing (W×D×H)	55×90×20 mm
Dimensions completely mounted (W×D×H)	55×90×20 mm

Measurement alignment	horizontal
Environmental conditions	

Use temperature [Min]	10 °C
Use temperature [Max]	40 °C
Storage temperature [Min]	-20 °C

Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	400×500×200 mm
Net weight	0,25 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,50 kg
Shipping weight	8 kg

Pictograms

STANDARD

