

# KERN OBB-A 1 107

**KERN**

N.A. „Swing-out” achromatic condenser (with aperture diaphragm)



## Category

|                  |                    |
|------------------|--------------------|
| Brand            | Optics             |
| Product category | Optical Instrument |

## Environmental conditions

|                           |       |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Readability force [d] (N)    | 1 d            |
| Dimensions packaging (W×D×H) | 80×80×70 mm    |
| Net weight                   | 0,3 kg         |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,30 kg        |
| Gross weight approx.         | 0,80 kg        |
| Shipping weight              | 0,8 kg         |

## Pictograms

STANDARD

