

KERN OBB-A 1251



Infinity planachromatic objective lens (without cover glass) 20 x /0,4, (8,35 mm) (sprung)

Pictograms

STANDARD



Category

| | |
|------------------|---------------------------|
| Brand | Optics |
| Product category | Optical Instrument |
| Product group | Microscope objective lens |

Construction

| | |
|-------------|---|
| Anti fungus | ✓ |
|-------------|---|

Environmental conditions

| | |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 65×40×40 mm |
| Net weight | 0,3 kg |
| Shipping method | Parcel service |
| Net weight approx. | 0,30 kg |
| Gross weight approx. | 0,60 kg |
| Shipping weight | 0,6 kg |

Objective

| | |
|----------------------------|---------------|
| Objective quality | Infinity Plan |
| Objective magnification | 20 x |
| Numerical Aperture | 0,4 |
| Objective working distance | 8,35 mm |