

# KERN OBB-A 1350

Eyepiece: WF 10 x / Ø 18 mm

# KERN

## Pictograms

### STANDARD



## Category

Brand	Optics
Product category	Optical Instrument
Product group	Microscope eyepiece

## Construction

Anti fungus	✓
-------------	---

## Ocular

Ocular field width	WF
Eye point	Standard
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm
Ocular scale	0,1 mm

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	85×65×45 mm
Net weight	0,1 kg
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,40 kg
Shipping weight	0,4 kg