

# KERN OBB-A 1382

Trinocular lens barrel

# KERN



## Pictograms

### STANDARD



## Category

Brand	Optics
Product category	Optical Instrument
Product group	Microscope Head

## Construction

Tube type	Butterfly
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Diopter adjustment	both-sided
Light distribution	100:0
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	50 mm

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	265×185×165 mm
Net weight	1,4 kg
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	2,0 kg
Shipping weight	2 kg