

KERN OBB-A 1516



100W HBO bulb for fluorescent unit from the range OCM 165

Pictograms

STANDARD



Category

Brand	Optics
Product category	Optical Instrument
Product group	Fluorescence unit

Power Supply

Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	20 V
Plug-in power supply type	Table power supply (separable)
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	410×390×310 mm
Net weight	8 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	9 kg
Shipping weight	9,9 kg