KERN OBE 121



Elegant, dynamic and impressive - the new all-round compound microscope for schools, training and laboratories



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Compound microscope
Product family	OBE-12

Approval	
CE mark	✓

Construction	
Dimension (W×D×H)	360×150×320 mm
Optical system	Finite
Tube type	Monocular
Tube angle of inclination	30°
Lens quality	achromatic
Standard objectives	4× 10× 40×
Nosepiece screw-in locations	4
Contrasting methods	Bright field Darkfield (optional) Polarisation (optional)
Colour temperature	6000 K

Ocular	
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

Focussing	
Fine drive minimum	0,002 mm
Torque regulation	✓
Field of view [Min]	0,18 mm
Field of view [Max]	4,5 mm
Focusing mechanism	coaxial coarse and fine drive

Illumination	
Illumination type incident light	none
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Aperture diaphragm	✓
Filter possible	✓

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH

Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	425×340×245 mm
Net weight	4,488 kg
Shipping method	Parcel service
Net weight approx.	4,6 kg
Gross weight approx.	6 kg
Shipping weight	7,1 kg

Objective	
Objectives - Details	Objective Achromatic 10 x / 0,25 anti-fungus Objective Achromatic 4

1

KERN OBE 121



Elegant, dynamic and impressive - the new all-round compound microscope for schools, training and laboratories

> x / 0,1 anti-fungus Objective Achromatic 40 x / 0,65 spring, antifungus

Pictograms

STANDARD











OPTION



