

# KERN OBE 124T241

# KERN

Our all-round compound microscope as a comprehensive digital solution for schools, training and laboratories



## Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OBE-S

## Approval

CE mark	✓
---------	---

## Display

Display resolution	2048×1536
--------------------	-----------

## Construction

Dimension (W×D×H)	360×235×540 mm
Optical system	Finite
Tube type	Siedentopf
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Lens quality	achromatic

	4×
Standard objectives	10×
	40×

Nosepiece screw-in locations	4
Eyepieces fixed	✓
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

Contrasting methods	Bright field
	Darkfield (optional)
	Polarisation (optional)

Light distribution	20:80
--------------------	-------

Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	50 mm
Colour temperature	6000 K
Camera type	Tablet camera
Camera sensor type	Sony CMOS
Camera sensor size	1/2,8"
Camera resolution	5 MP
Camera colour depth	Colour
Camera framerate	30 fps
Camera mounting types	C-mount thread
Camera - exposure method	Rolling Shutter

## Ocular

Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

## Focussing

Fine drive minimum	0,002 mm
Torque regulation	✓
Field of view [Min]	0,18 mm
Field of view [Max]	4,5 mm
Focusing mechanism	coaxial coarse and fine drive

## Illumination

Illumination type incident light	none
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Illumination dimmable	Transmitted light
Filter possible	✓

## Functions

Memory - total size	128 GB
	WiFi standard
Interfaces	USB 2.0
	HDMI
	MicroSD card slot
Supported operating systems	Android
Camera - applicable software	integrated

## Power Supply

Input voltage power supply / power [Max]	100 - 240 V
--	-------------

# KERN OBE 124T241



Our all-round compound microscope as a comprehensive digital solution for schools, training and laboratories

Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	560×440×330 mm
Net weight	5,978 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	16,3 kg

## Pictograms

### STANDARD



### OPTION

