## KERN OBL 137T241

## The digital laboratory assistant with infinity optical unit and fixed, Koehler illumination



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Digital microscope set
Product family	OBL-S
Annroual	
Approval	
CE mark	$\checkmark$
Display	
	LCD touch
Display type	LCD touch
Display type	
Display screen size	9,7" 2048×1536
Display resolution	2046*1550
Construction	
Dimension (W×D×H)	394×235×600 mm
Optical system	Infinity
Tube type	Siedentopf
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	$\checkmark$
Lens quality	Infinity E-Plan
Standard objectives	4× 10× 40× 100×
Nosepiece screw-in locations	4
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

Contrasting methods	Bright field Darkfield (optional) Polarisation (optional) Fluorescent (optinal) Phase contrast (optional)
Light distribution	20:80
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	50 mm
Camera type	Tablet camera
Camera sensor type	Sony CMOS
Camera sensor size	1/2,8"
Camera resolution	5 MP
C-Mount focusable	
C-Mount magnification	0,5 x
Camera colour depth	Colour
Camera framerate	30 fps C-mount thread
Camera mounting types	
Camera - exposure method	Rolling Shutter
Ocular	
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	23,2 mm
Focussing	
Fine drive minimum	0,002 mm
Torque regulation	J
Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Focusing mechanism	coaxial coarse and fine
	drive
Illumination	
Illumination type incident light	none
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Field diaphragm	1
Aperture diaphragm	✓
Koehler illumination	1
Filter possible	1
Functions	
Interfaces	WiFi standard USB 2.0

KERN



1

## KERN OBL 137T241



The digital laboratory assistant with infinity optical unit and fixed, Koehler illumination

	HDMI MicroSD card slot
Supported operating systems	Android
Camera - applicable software	integrated
Power Supply	
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Net weight	7,278 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	20,2 kg
Pictograms	