

KERN OBL 156



High-quality phase contrast microscope – specially pre-configured with a series of options for flexible expansion



Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBL-15

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	394×185×377 mm
Optical system	Infinity
Tube type	Siedentopf
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Lens quality	Infinity E-Plan / Plan
	4×
Standard objectives	100×
	PH 10×
	PH 40×
Nosepiece screw-in locations	4
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Contrasting methods	Bright field Darkfield (optional) Phase contrast Polarisation (optional) Fluorescent (optional)
Light distribution	20:80
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	50 mm

Ocular

Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

Focussing

Fine drive minimum	0,002 mm
Torque regulation	✓
Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Focusing mechanism	coaxial coarse and fine drive

Illumination

Illumination type incident light	none
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Illumination dimmable	Transmitted light
Field diaphragm	✓
Phase-contrast unit	PH condenser for single slot
Filter possible	✓

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK US CH

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
---------------------------	-----

KERN OBL 156



High-quality phase contrast microscope – specially pre-configured with a series of options for flexible expansion

Dimensions packaging (W×D×H)	420×275×450 mm
Net weight	5,488 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	10,4 kg

Objective

Objectives - Details	PH-Objective Infinity Plan 10 x / 0,25 anti-fungus Objective Infinity E-Plan 100 x / 1,25 oil, spring, anti-fungus Objective Infinity E-Plan 4 x / 0,1 anti-fungus PH-Objective Infinity Plan 40 x / 0,66 spring, anti- fungus
----------------------	---

Pictograms

STANDARD



OPTION

