KERN **OBN 135C825**



The digital laboratory assistant with infinity optical unit and fixed, Koehler illumination



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Digital microscope set
Product family	OBN-S

Approval	
CE mark	✓

Construction	
Dimension (W×D×H)	390×200×470 mm
Optical system	Infinity
Tube type	Siedentopf
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Lens quality	Infinity Plan
Standard objectives	4× 10× 20× 40× 100×
Nosepiece screw-in locations	5
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Contrasting methods	Bright field Darkfield (optional) Polarisation (optional) Fluorescent (optinal) Phase contrast (optional)
Light distribution	100:0
Interpupillary distance [Max]	75 mm

Interpupillary distance [Min]	50 mm
Colour temperature	6000 K
Camera type	USB2 Microscope camera - C-Mount
Camera sensor type	CMOS
Camera sensor size	1/2,5"
Camera resolution	5,1 MP
Camera colour depth	Colour
Camera framerate	6,8 - 55 fps
Camera mounting types	C-mount thread
Camera - exposure method	Rolling Shutter

Ocular	
Ocular field width	HWF
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

Focussing	
Fine drive minimum	0,002 mm
Torque regulation	✓
Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Focusing mechanism	coaxial coarse and fine drive

Illumination	
Illumination type incident light	none
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Field diaphragm	✓
Koehler illumination	✓
Filter possible	✓

Functions	
Interfaces	USB 2.0
Supported operating systems	Win XP Win Vista Win 7 Win 8 Win 10
Camera - applicable software	external (OXM 901, OXM 902)

1

KERN **OBN 135C825**



The digital laboratory assistant with infinity optical unit and fixed, Koehler illumination

Power Supply	
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH

Environmental conditions		
Storage temperature [Min]	-5 °C	
Storage temperature [Max]	40 °C	

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Net weight	10,763 kg
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	14 kg
Shipping weight	20,2 kg

Pictograms