## KERN ODC 832



Specialists in microscopy for measurement, counting, documentation, archiving and image processing



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Microscope camera
Product family	ODC-83

Approval		
CE mark	✓	

Construction	
Dimension (W×D×H)	80×80×45 mm
Material display housing	No display available
Camera type	USB3 Microscope camera - C-Mount
Camera sensor type	Aptina CMOS
Camera sensor size	1/2,5"
Camera resolution	5,1 MP
Camera colour depth	Colour
Camera mounting types	C-mount
Camera - exposure method	Rolling Shutter

Functions	
Interfaces	USB 3.0
Supported operating systems	Win XP Win Vista Win 7 Win 8 Win 10 Linux
Camera - applicable software	external (OXM 902)

## Power Supply

Input voltage device / power [Max] 5 V, 200 mA

Environmental conditions		
Storage temperature [Min]	-5 °C	
Storage temperature [Max]	40 °C	

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	164×164×75 mm
Net weight	0,5829 kg
Shipping method	Parcel service
Net weight approx.	0,60 kg
Gross weight approx.	1,00 kg
Shipping weight	1 kg

## Pictograms

## **STANDARD**





1