KERN ODC 841



Specialists in microscopy for measurement, counting, documentation, archiving and image processing



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Microscope camera
Product family	ODC-84

Approval		
CE mark	✓	

Construction	
Dimension (W×D×H)	68×68×46 mm
Camera type	USB3 Microscope camera - C-Mount
Camera sensor type	Sony CMOS
Camera sensor size	1"
Camera resolution	20 MP
Camera colour depth	Colour
Camera mounting types	C-mount
Camera - exposure method	Rolling Shutter

Functions	
Interfaces	USB 3.0
Supported operating systems	Win XP Win Vista Win 7 Win 8 Win 10 Linux
Camera - applicable software	external (OXM 902)

Power Supply	
Input voltage device / power [Max]	5 V, 435 mA

Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	150×150×100 mm
Net weight	0,46 kg
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	0,65 kg
Shipping weight	0,6245 kg

Pictograms

STANDARD





1