KERN OSE 409



Predefined stereo microscope set with swivel arm and gooseneck illumination unit for your functional workstation



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Stereo microscope set
Product family	OSE-4

Approval	
CE mark	✓

Construction	
Dimension (W×D×H)	428×132×344 mm
Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	45°
Standard objectives	1×
Eyepieces fixed	✓
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Contrasting methods	Bright field
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	55 mm

Ocular	
Ocular field width	WF
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	30,5 mm

Focussing	
Torque regulation	✓
Working distance	250 mm
Field of view [Max]	20 mm
Focusing mechanism	coarse drive

mummation	
Illumination type incident light	LED
Illumination intensity incident light	3 W
Illumination type transmitted light	None
Illuminance	Reflected light

Power Supply	
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH

Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	435×410×200 mm
Net weight	6,49 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	8 kg
Shipping weight	7,5 kg

Pictograms

1