

KERN OZL 45 1

KERN

Stereo zoom microscope with halogen illumination, for the laboratory, training centres, quality control or agriculture



Zoom [Min]	0,75 x
Zoom [Max]	5 x
Magnification ratio	6,7:1
Field of view [Min]	5 mm
Field of view [Max]	33 mm
Focusing mechanism	coarse drive
Sample height [Max]	120 mm
Standard total magnification [Min]	7,5 x
Standard total magnification [Max]	50 x

Illumination

Illumination type incident light	Halogen
Illumination intensity incident light	10 W
Illumination intensity transmitted light	10 W
Illumination type transmitted light	Halogen
Illuminance	Reflected light Transmitted light

Power Supply

Input voltage power supply / power [Max]	220 V
Input voltage device / power [Max]	220 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK CH

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	475×345×320 mm
Net weight	4,585 kg
Shipping method	Parcel service
Net weight approx.	4,6 kg
Gross weight approx.	6 kg
Shipping weight	10,5 kg

Category

Brand	Optics
Product category	Microscope
Product group	Stereo microscope
Product family	OZL-45

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	330×270×460 mm
Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Contrasting methods	Bright field
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	55 mm

Ocular

Ocular field width	HSWF
Ocular magnifications	10 x
Ocular visual field	23 mm
Ocular diameter	30 mm

Focussing

Torque regulation	✓
Working distance	113 mm

KERN OZL 451



Stereo zoom microscope with halogen illumination, for the laboratory, training centres, quality control or agriculture

Pictograms

STANDARD

