KERN OZL 468C825



The flexible, affordable all-rounder with zoom function as a digital solution for schools, training companies, inspection authorities and laboratories.



		Fiel
Category		Fiel
		Foc
Brand	Optics	San
Product categoriy	Microscope	
Product group	Digital microscope set OZL-S	Illu
Product family	021-5	Illur
Approval		Illur
CE mark	1	Illur
	•	ligh
Construction		Illur Illur
Dimension (W×D×H)	300×240×490 mm	mu
Optical system	Greenough	Illur
Tube type	Trinocular	
Tube angle of inclination	45°	_
Tube 360° rotation	+0 ✓	Fur
Eyepieces fixed	✓ ✓	Inte
Diopter adjustment	both-sided	
Diopter adjustment [Min]	-5	
Diopter adjustment [Max]	5	Sup
Contrasting methods	Bright field	
Light distribution	100:0	
Interpupillary distance [Max]	75 mm	Car
Interpupillary distance [Min]	55 mm	
Camera type	USB2 Microscope camera - C-Mount	Pov
Camera sensor type	CMOS	Inpi pov
Camera sensor size	1/2,5"	Inpi
Camera resolution	5 MP	Plu
Camera colour depth	Colour	Sup
Camera framerate	6,8 - 55 fps	Plu
Camera mounting types	C-mount thread	cou
Camera - exposure method	Rolling Shutter	deli

Ocular	
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	30 mm
Focussing	
Torque regulation	1
Working distance	105 mm
Zoom [Min]	0,7 x
Zoom [Max]	4,5 x
Magnification ratio	6,4:1
Field of view [Min]	4,4 mm
Field of view [Max]	28,6 mm
Focusing mechanism	coarse drive
Sample height [Max]	140 mm
Illumination	
Illumination type incident light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Illumination dimmable	Incident light + Transmitted light, separate
Functions	
Interfaces	USB 2.0
Supported operating systems	Win XP Win Vista Win 7 Win 8 Win 10
Camera - applicable software	external (OXM 901, OXM 902)
Power Supply	
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for	
countries - included with the delivery	EURO

KERN OZL 468C825



The flexible, affordable all-rounder with zoom function as a digital solution for schools, training companies, inspection authorities and laboratories.

Plug-in power supply / adapter for countries - optional	AUS UK US CH
Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Net weight	4,865 kg
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	7 kg
Shipping weight	20,2 kg

Pictograms