

KERN OZL 961UK

KERN

Predefined stereo microscope set with simple telescopic arm and 4.5 W ring illumination unit for greater flexibility at the workstation



Category

Brand	Optics
Product category	Microscope
Product group	Stereo microscope set
Product family	OZL-9

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	700×255×600 mm
Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Contrasting methods	Bright field
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	55 mm

Ocular

Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	30 mm

Focussing

Torque regulation	✓
-------------------	---

Working distance	100 mm
------------------	--------

Zoom [Min]	0,7 x
------------	-------

Zoom [Max]	4,5 x
------------	-------

Magnification ratio	6,4:1
---------------------	-------

Field of view [Min]	4,4 mm
---------------------	--------

Field of view [Max]	28,6 mm
---------------------	---------

Focusing mechanism	coarse drive
--------------------	--------------

Sample height [Max]	140 mm
---------------------	--------

Standard total magnification [Min]	7 x
------------------------------------	-----

Standard total magnification [Max]	45 x
------------------------------------	------

Illumination

Illumination type incident light	LED
----------------------------------	-----

Illumination intensity incident light	4,5 W
---------------------------------------	-------

Illuminance	Reflected light
-------------	-----------------

Illumination dimmable	Incident light
-----------------------	----------------

Power Supply

Input voltage power supply / power [Max]	100 - 240 V
--	-------------

Input voltage device / power [Max]	100 - 240 V
------------------------------------	-------------

Plug-in power supply type	Built-in power supply
---------------------------	-----------------------

Supplied power supply	Power supply unit
-----------------------	-------------------

Plug-in power supply / adapter for countries - included with the delivery	UK
---	----

Environmental conditions

Storage temperature [Min]	-5 °C
---------------------------	-------

Storage temperature [Max]	40 °C
---------------------------	-------

Packing & Shipping

Readability force [d] (N)	1 d
---------------------------	-----

Dimensions packaging (W×D×H)	820×420×240 mm
------------------------------	----------------

Net weight	17 kg
------------	-------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	17 kg
--------------------	-------

Gross weight approx.	20 kg
----------------------	-------

Shipping weight	19,5 kg
-----------------	---------

Pictograms