## KERN OZP 558C832



First-class optics as well as strong illumination combined with a high level of flexibility and digital tools



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Digital microscope set
Product family	OZP-S
Approval	
CE mark	1
GEIIIdIK	V
Construction	
Dimension (W×D×H)	330×285×540 mm
Optical system	Greenough
Tube type	Trinocular
Tube angle of inclination	35°
Tube 360° rotation	$\checkmark$
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6
Contrasting methods	Bright field Darkfield (optional)
Light distribution	100:0
Interpupillary distance [Max]	76 mm
Interpupillary distance [Min]	52 mm
Camera type	USB3 Microscope camera - C-Mount
Camera sensor type	CMOS
Camera sensor size	1/2,5"
Camera resolution	5,1 MP
Camera colour depth	Colour
Camera framerate	14,2 - 101,2 fps
Camera mounting types	C-mount thread
Camera - exposure method	Rolling Shutter

Ocular	
Ocular field width	HSWF
Ocular magnifications	10 x
Ocular visual field	23 mm
Ocular diameter	30 mm
Focussing	
Torque regulation	1
Working distance	108 mm
Zoom [Min]	0,6 x
Zoom [Max]	5,5 x
Magnification ratio	9,2:1
Field of view [Min]	4,2 mm
Field of view [Max]	38,3 mm
Focusing mechanism	coarse drive
Sample height [Max]	110 mm
Illumination	
Illumination type incident light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Reflected light Transmitted light
Illumination dimmable	Incident light + Transmitted light, separate
Functions	
Interfaces	USB 3.0
Supported operating systems	Win XP Win Vista Win 7 Win 8 Win 10
Camera - applicable software	external (OXM 901, OXM 902)
Power Supply	
Input voltage power supply / power [Max]	110 - 220 V
Input voltage device / power [Max]	110 - 220 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO

# KERN OZP 558C832



First-class optics as well as strong illumination combined with a high level of flexibility and digital tools

	AUS
Plug-in power supply / adapter for	UK
countries - optional	US
	СН

#### Environmental conditions

Storage temperature [Min]-5 °CStorage temperature [Max]40 °C

### Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Net weight	5,4616 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	20,2 kg

### Pictograms