

KERN OZP 558T24 1



First-class optics as well as strong illumination combined with a high level of flexibility and digital tools



Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OZP-S

Approval

CE mark	✓
---------	---

Display

Display type	LCD touch
Display type	LCD touch
Display screen size	9,7"
Display resolution	2048×1536

Construction

Dimension (W×D×H)	330×285×690 mm
Optical system	Greenough
Tube type	Trinocular
Tube angle of inclination	35°
Tube 360° rotation	✓
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6
Contrasting methods	Bright field Darkfield (optional)
Light distribution	100:0
Interpupillary distance [Max]	76 mm
Interpupillary distance [Min]	52 mm
Camera adapter type	C-Mount
Supported camera types	Microscope Camera
Camera type	Tablet camera

Camera sensor type	Sony CMOS
Camera sensor size	1/2,8"
Camera resolution	5 MP
C-Mount focusable	✓
C-Mount magnification	0,5 x
Camera colour depth	Colour
Camera framerate	30 fps
Camera mounting types	C-mount thread
Camera - exposure method	Rolling Shutter

Ocular

Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	23 mm
Ocular diameter	30 mm

Focussing

Torque regulation	✓
Working distance	108 mm
Zoom [Min]	0,6 x
Zoom [Max]	5,5 x
Magnification ratio	9,2:1
Field of view [Min]	4,2 mm
Field of view [Max]	38,3 mm
Focusing mechanism	coarse drive
Sample height [Max]	110 mm

Illumination

Illumination type incident light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Reflected light Transmitted light

Functions

Memory - total size	128 GB
Interfaces	WiFi standard USB 2.0 HDMI MicroSD card slot
Supported operating systems	Android
Camera - applicable software	integrated

KERN OZP 558T24 1



First-class optics as well as strong illumination combined with a high level of flexibility and digital tools

Power Supply

Input voltage power supply / power [Max]	110 - 220 V
Input voltage device / power [Max]	110 - 220 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Net weight	5,6716 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	20,2 kg

Pictograms