

KERN PFB-A03

Power supply PFB-A03 (UK)

KERN



Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Approval

CE mark	✓
---------	---

Construction

Material	plastic
Cable length	1,8 m

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	UK

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	95×80×50 mm
Net weight	0,0905 kg
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,15 kg
Shipping weight	0,1056 kg