

# KERN PLS-A06

# KERN

Adapter



## Pictograms

### STANDARD



## Category

Brand	KERN
Product category	Balance
Product group	Power adapter

## Approval

CE mark	✓
---------	---

## Construction

Material	plastic
----------	---------

## Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	11 V AC, 1100 mA
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	UK

## Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	95×75×60 mm
Net weight	0,35 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	0,40 kg
Shipping weight	0,382 kg