## KERN SP 200K



Compact photometer, optimised for accurate light measurement, including LED light measurement



Category	
Brand	Sauter
Product categoriy	Environment/ Occupational safety
Product group	Light measuring instrument
Product family	SP

Measuring System	
Units	lx fc
Tolerance (% of [Max])	5%
Measuring head measuring frequency	2 Hz
Measuring range [Max] (Lux)	200 lx; 2000 lx; 20000 lx; 200000 lx
Readability illumination [d] (lx)	0,1 lx; 1 lx; 10 lx; 100 lx

Approval		
CE mark	✓	

Display	
Display type	LCD
Display digit height	16 mm
Construction	

Dimension housing (W×D×H)	185×68×38 mm
Dimensions completely mounted (W×D×H)	185×68×38 mm
Material display housing	Plastics
Material housing	plastic

Functions	
Hold function	✓

Peak function	✓
---------------	---

Power Supply	
Supplied power supply	Battery
Battery	9 V block
Battery / accumulator type	Alkali(-Manganese)
Battery connection	9V Bloc
Battery operating time	200 h

Environmental conditions		
Storage temperature [Min]	-10 °C	
Storage temperature [Max]	50 °C	

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	200×106×55 mm
Net weight	0,13 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,30 kg
Shipping weight	0,28 kg

Services (optional)	
Article number for factory calibration	961-190

## Pictograms

STANDARD



**OPTION** 

