KERN **TI-AC**



Lever operated test stand for hardness testing with base plate made of glass



Category	
Brand	Sauter
Product categoriy	Hardness testing
Product group	Manual Shore test stand
Product family	TI
Measuring System	
Test force Hardness measurement	10 N
Hardness scales	Shore A
Construction	
Base plate diameter (Ø)	75 mm
Dimensions completely mounted (W×D×H)	150×200×330 mm
Material housing	stainless steel
Traverse distance with lever movement / release [Max]	15 mm
Test object height [Max]	60 mm
Environmental conditions	
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C
Decking & Chinning	
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	355×255×180 mm
Net weight	5 kg
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	7 kg
Shipping weight	6,3 kg

Pictograms

STANDARD

