KERN TI-ACL



Lever operated test stand for hardness testing with base plate made of glass



Pictograms

STANDARD





Category	
Brand	Sauter
Product categoriy	Hardness testing
Product group	Manual Shore test stand
Product family	TI

Measuring System	
Test force Hardness measurement	10 N
Hardness scales	Shore A

Construction	
Base plate diameter (Ø)	75 mm
Dimensions completely mounted (W×D×H)	150×200×580 mm
Material housing	metal, lacquered
Traverse distance with lever movement / release [Max]	15 mm
Test object height [Max]	290 mm

Environmental conditions	
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	355×255×180 mm
Net weight	5,7 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	7 kg
Shipping weight	7 kg