## KERN TI-DL



Lever operated test stand for hardness testing with base plate made of glass



## Pictograms

## **STANDARD**





Category	
Brand	Sauter
Product categoriy	Hardness testing
Product group	Manual Shore test stand
Product family	TI

## Measuring System Test force Hardness measurement 50 N Shore D Hardness scales

Construction	
Base plate diameter (Ø)	75 mm
Dimensions completely mounted (W×D×H)	150×200×580 mm
Material housing	metal, lacquered
Traverse distance with lever movement / release [Max]	15 mm
Test object height [Max]	290 mm

Environmental conditions	
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	355×255×180 mm
Net weight	8,7 kg
Shipping method	Parcel service
Net weight approx.	9 kg
Gross weight approx.	11 kg
Shipping weight	10,2 kg