

KERN TVP-L



Manual test stand for compressive force measurements with digital length measurement



Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	570×275×240 mm
Net weight	10,5 kg
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	12 kg
Shipping weight	12 kg

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Test bench
Product group	Manual test stand
Product family	TVP-L

Measuring System

Measurable length [Max]	10 cm
Tolerance (measured length)	2%

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	150×233×420 mm
Dimension housing (W×D×H)	150×233×420 mm
Dimensions completely mounted (W×D×H)	150×233×420 mm
Material housing	metal, lacquered
Generated force [Max]	500 N
Mounting - force application	5 × threaded hole M6
Mounting - force dissipation	5 × threaded hole M6
Type of drive	manual lever
Traverse distance with lever movement / release [Max]	78 mm
Measuring room height [Max]	315 mm

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C