#### KERN UID 3000K-0DM



High-resolution multi-range pallet scale with a wide range of interfaces, verification optional



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Pallet scale
Product family	UID

#### Measuring System

0,				
Conformity assessment possible	✓			
Construction type of the scale	Multi-range balance			
Number of weighing ranges	2			
Weighing system	Strain gauge			
Weighing capacity [Max]	1500 kg; 3000 kg			
Readability [d]	0,5 kg; 1 kg			
Resolution	3.000, 3.000			
Linearity	± 1,5 kg; 3 kg			
Reproducibility	0,5 kg; 1 kg			
Tare range	-3000 kg			
Default unit	kg			
Units	kg g Ib oz PCS tJ HJ			
Units (if device is conformity assessed)	kg			
Minimum weight [Min]	10 kg; 20 kg			
Adjustment options	Adjusting with external weight			
Stabilization time	4 s			
Warm-up time	10 min; 10 min			
Eccentric loading at 1/3 [Max]	2,5 kg; 5 kg			

Loadcell type	KELI-SQB-1500kg			
Load cell connection	4-wire			
Approval				
CE mark	1			
Pattern approval for conformity	1			
assessment	•			
Accuracy classe				
Verification scale interval [e]	0,5 kg; 1 kg			
Conformity assessment possible ex works	1			
Display				
Display type	LCD			
Display type	LCD			
Display screen size	110×35 mm			
Display backlight	✓			
Display digit height - smallest digit	25 mm			
Display digit height	25 mm			
Languages of the user interface	Symbol language			
Construction				
Dimension display device (W×D×H)	268×115×80 mm			
Dimensions weighing platform (W×D×H)	1190×840×110 mm			
Material display housing	Plastics			
Material weighing plate	steel, powder-coated			
Material platform	steel, powder-coated			
Dimensions weighing surface (W×D)	1195×840 mm			
Cable length	5 m			
Display device cable length	5 m			
Allowed cable length display device [Max]	15 m			
Material load cell(s)	alloyed steel			
Load cells - number	4			
Levelling feet adjustable				
Wall mount	J			
Stand inclinable	<i>√</i>			
Functions				
Number of keys for operation	4			
Auto-off interval(s) in mains power mode	3 min off 5 min 30 min 15 min			

### KERN UID 3000K-0DM



# High-resolution multi-range pallet scale with a wide range of interfaces, verification optional

Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min			
Time display	$\checkmark$			
Tare function	manual (single)			
Hold function	$\checkmark$			
Percentage determination	$\checkmark$			
Counting function	✓			
Tolerance weighing				
Tolerance weighing - type of signal	visual			
Function for averaging under unstable weighing conditions	1			
Recipe/summing level	Sum A			
Alibi memory	optional internal memory			
Alibi memory - number of memory spaces	250.000			
Interfaces	RS-232 standard Ethernet (optional, factory) USB (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) USB-Host/Master (optional, factory) Verification plug (optional, factory) Bluetooth BLE (v4.0) (optional, factory)			
IP protection - display	IP65			
IP protection - load cell	IP67			
Counting				
Reference quantity	10, 20, 50, 100, 200			
Power Supply				
Input voltage power supply / power [Max] Input voltage device / power [Max] Plug-in power supply type	100 V - 240 V AC 50/60 Hz 0.4 A max 12 V DC, 1000 mA Power adapter			
Supplied power supply	Power supply unit			
Plug-in power supply / adapter for	EURO			

UK US

intern

3 h

Rchrg. battery optional -

countries - included with the

Rechargeable battery optional

Rechargeable battery charging

delivery

time

Rechargeable battery operating time - backlight on	26 h			
Rechargeable battery operating time - backlight off	43 h			
Battery	no battery			
Battery / accumulator type	Pb			
Environmental conditions				
Humity of environment [Min]	10 %			
Humity of environment [Max]	95 %			
Ambient temperature [Min]	-10 °C			
Ambient temperature [Max]	40 °C			
Packing & Shipping				
Readability force [d] (N)	2 d			
Dimensions packaging (W×D×H)	1240×890×250 mm			
Net weight	44 kg			
Shipping method	Freight			
Net weight approx.	44 kg			
Gross weight approx.	75 kg			
Shipping weight	74 kg			
Services (optional)				
Article number for adjustment at the location of installation	961-252			
Article number for conformity assessment	965-232			
	965-232 963-132			

## KERN UID 3000K-0DM



High-resolution multi-range pallet scale with a wide range of interfaces, verification optional

Pictograms

STANDARD

CAL EXT	• 600 • RS 232		PCS	SUM	% Percent	-√+ ⊙ ৢৢৢৢ TOL
MOVE	• IP 65	<b>6</b> 1P 67	DMS	2 DAYS		

OPTION



FACTORY

