## KERN YKA-10



Mains adapter 100 V - 240 V, 50 / 60 Hz, standard EURO/US/AUS/UK/CH



## Pictograms

## **STANDARD**



Category	
Brand	KERN
Product categoriy	Balance
Product group	Power adapter

Approval	
CE mark	✓

Construction		
Material	plastic	

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	15 V, 2.1 A
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US

Environmental conditions	
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	70×70×70 mm
Net weight	0,725 kg
Shipping method	Parcel service
Net weight approx.	0,75 kg
Gross weight approx.	0,90 kg
Shipping weight	0,87 kg

1