KERN YKV-02

KERN

Modern digital weighing transmitter for the rapid recording of weighing data and forwarding it to the most varied output channels such as tablets, networks, SPS controllers, etc. - ideal for operating balances in systems or conveyors



Category	
Brand	KERN
Product categoriy	Component
Product group	Digital weighing transmitter
Product family	YKV

Measuring System	
Number of weighing ranges	1
Terminal resolution (not verifiable)	60.000
Linearity	±
Units	kg g t
Adjustment options	Adjusting with external weight

Construction	
Dimension display device (W×D×H)	100×140×35 mm
Dimension housing (W×D×H)	100×140×35 mm
Material display housing	Plastics

Functions	
PreTare function	✓
Tare function	manual (multi)
Interfaces	RS-232 standard USB WiFi (optional, factory) Bluetooth BLE (v4.0) (optional, factory)
IP protection - display	no IP protection

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / nower [May]	5 V 1000 mA

Plug-in power supply type	USB including power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Battery	no battery


Environmental conditions	
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	215×150×72 mm
Net weight	0,339 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	0,50 kg
Shipping weight	0,5 kg

Services (optional)	
Article number for adjustment at the location of installation	auf Anfrage on request

Pictograms

STANDARD



OPTION



FACTORY



