

76.22SLS



| | |
|----------|-----|
| B [mm]: | 32 |
| d [mm]: | 15 |
| d1 [mm]: | 14 |
| H [mm]: | 48 |
| L [mm]: | 230 |
| L1 [mm]: | 57 |
| [g]: | 600 |

