

76.24SLS

| | |
|----------|------|
| B [mm]: | 34.5 |
| d [mm]: | 18 |
| d1 [mm]: | 16 |
| H [mm]: | 54 |
| L [mm]: | 250 |
| L1 [mm]: | 67 |
| [g]: | 795 |

