



PowerMaxx SB Basic Set with 41-piece mobile workshop

- Light, compact cordless hammer drill with extremely compact design for versatile use
- Hammer drill function for drilling in masonry
- Mobile workshop (41 pieces): 5 wood drill bits (4/5/6/8/10mm), 14 HSS drill bits (1.5/1.5/2/2/2.5/3/3/3.5/4/4.5/5/5.5/6/6.5mm), 20 screwdriver bits length 25mm (PH1/PH2/PH2/PH3/PZ1/PZ2/PZ2/PZ2/PZ3/H3/H4/H5/H6/T15/T20/T25/T30/S4/S5/S6), bit holder (60mm), cutter knife with 2 spare blades
- Integrated working light to illuminate the contact area
- Practical capacity display for checking the charge status
- Handy belt hook, can be fixed either on the right or left side

Order no. EAN code	600385710 4061792249455
Type of battery pack	Li-Power
Battery voltage	12 V
Battery pack capacity	2 x 2 Ah
Maximum torque, soft	17 Nm / 150 in-lbs
Maximum torque, hard	34 Nm / 301 in-lbs
Adjustable torque	0.5 - 5 Nm // 4.4 - 44.3 in-lbs
Drill-Ø masonry	10 mm / 3/8 "
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	18 mm / 23/32 "
No-load speed	0 - 360 / 0 - 1400 rpm
Maximum impact rate	21000 bpm
Chuck capacity	1.5 - 10 mm // 1/16 - 3/8 "
Weight without battery pack	0.82 kg / 1.8 lbs
Weight with battery pack	1.01 kg / 2.2 lbs

Scope of delivery

Keyless chuck, Belt hook, 2 Li-Power push-in battery packs (12 V/2.0 Ah), Charger LC 40, Plastic carry case, Accessory set