



ST 18 L 90

- The daily helper for universal sawing applications: compact cordless jigsaw for cuts in wood up to 90 mm
- Best ergonomics in all working positions and soft-grip surface for perfect handling and safe guidance of the saw
- Metabo "Quick" for changing saw blades without tools and with automatic ejection
- Efficient chip blowing function for clear view of the cutting line
- Integrated LED work light for illumination of the cutting line
- Restart protection: prevents unintentional start-up after battery pack change
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601047840
EAN code	4061792256644

Type of battery pack	Li-Power / LiHD
Battery voltage	18 V
Cutting depth wood	90 mm / 3 9/16 "
Cutting depth NF metal	25 mm / 1 "
Cutting depth sheet steel	10 mm / 3/8 "
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	750 - 3000 rpm
Saw blade stroke	22 mm / 7/8 "
Weight without battery pack	1.5 kg
Weight with battery pack	1.9 kg

Scope of delivery

Extraction nozzle, Protective glass, Chip guard plate, 3 Saw blades, Hexagonal wrench, metaBOX 145 L, without battery pack, without charger