



ST 18 LT 130 BL

- The versatile one for interior development and assembly: compact cordless jigsaw with powerful Brushless motor for fast, precise cuts
- Best ergonomics in all working positions and soft-grip surface for perfect handling and safe guidance of the saw
- Powerful Brushless motor for quick work progress and highest efficiency
- Metabo "Quick" for changing saw blades without tools and with automatic ejection
- Efficient chip blowing function for clear view of the cutting line
- Integrated LED work light, can be switched off for cuts from below without getting blinded by the light
- Restart protection: prevents unintentional start-up after battery pack change
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601054850
EAN code	4061792258976

Type of battery pack	LiHD
Battery voltage	18 V
Cutting depth wood	130 mm / 5 1/8 "
Cutting depth NF metal	35 mm / 1 3/8 "
Cutting depth sheet steel	10 mm / 3/8 "
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	1000 - 3500 rpm
Saw blade stroke	22 mm / 7/8 "
Weight without battery pack	1.5 kg
Weight with battery pack	2 kg

Scope of delivery

Extraction nozzle, Protective glass, Plastic guard plate, Chip guard plate, 3 Saw blades, Hexagonal wrench, without battery pack, without charger