



## STB 18 LT 130 BL

- The versatile one for interior development and assembly: compact cordless jigsaw with powerful Brushless motor for fast, precise cuts
- Best ergonomics in all working positions and soft-grip surface for perfect handling and safe guidance of the saw
- Metabo "Quick" for changing saw blades without tools and with automatic ejection
- Top handle with non-slip soft-grip surface
- Efficient chip blowing function for clear view of the cutting line
- Integrated LED work light for illumination of the cutting line
- Restart protection: prevents unintentional start-up after battery pack change
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

<b>Order no.</b>	<b>601055850</b>
<b>EAN code</b>	<b>4061792258990</b>

Type of battery pack	LiHD
Battery voltage	18 V
Cutting depth wood	130 mm / 5 1/8 "
Cutting depth NF metal	35 mm / 1 3/8 "
Cutting depth sheet steel	10 mm / 3/8 "
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	3500 rpm
Saw blade stroke	22 mm / 7/8 "
Weight without battery pack	1.5 kg
Weight with battery pack	2 kg

### Scope of delivery

Extraction nozzle, Protective glass, Plastic guard plate, Chip guard plate, 3 Saw blades, Hexagonal wrench, without battery pack, without charger