



STAB 18 LTX 150 BL

- The power pack for demanding applications: Cordless jigsaw with maximum cutting output thanks to powerful Brushless motor and constant strokes under load
- Powerful Brushless motor for quick work progress and highest efficiency
- Metabo "Quick" for changing saw blades without tools and with automatic ejection
- Low-lying saw blade guidance for precise cuts
- Top handle with non-slip soft-grip surface
- Efficient chip blowing function for clear view of the cutting line
- Integrated LED work light for illumination of the cutting line
- Restart protection: prevents unintentional start-up after battery pack change
- Long service life thanks to optimum gear and motor design and robust die-cast aluminium gear housing
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Splinter-free and gentle sawing due to guard plate and chip break guard
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601503850
EAN code	4061792234055

Type of battery pack	LiHD
Battery voltage	18 V
Cutting depth wood	150 mm / 5 29/32 "
Cutting depth NF metal	35 mm / 1 3/8 "
Cutting depth sheet steel	10 mm / 3/8 "
Swivel range from / to:	- 45 / + 45 °
Pendulum stroke levels	4
Strokes in idle	1000 - 3500 rpm
Saw blade stroke	26 mm / 1 1/32 "
Weight without battery pack	2 kg / 4.4 lbs
Weight with battery pack	2.6 kg / 5.7 lbs

Scope of delivery

Extraction nozzle, Protective glass, Plastic guard plate, Chip guard plate, 3 Saw blades, Hexagonal wrench