



## AS 36-18 M 30 PC-CC with manual filter cleaning and CordlessControl

- Compact cordless vacuum cleaner of dust class M with integrated filter cleaning for versatile application
- CordlessControl: the vacuum cleaner starts/stops automatically when the cordless tool from Metabo or other brands, which is connected to the hose, is switched on/shutting down
- Compact vacuum cleaner for liquids and dry solids with commercial registration
- High user safety: certified in accordance with EU standard for dust class M
- PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks
- Eco mode for longer runtime per battery pack charge, boost mode for maximum power
- Automatic trailing mechanism for emptying the suction hose completely
- Suction stop when vacuuming liquids once the maximum fill level is reached
- Warning signal on shortfall of the minimum volume flow to protect the user
- Basic antistatic equipment prevents static charge when using appropriate accessories
- Fast coupling of metaBOXes with tools and accessories on the vacuum cleaner for easy change of location
- Supplied vacuum cleaner accessories with quick system for fast retrofitting when in use
- Easy transport thanks to hose holder and storage for pipes and nozzles
- Dust-proof and splash-proof battery pack compartment with lockable flap
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	602074850
EAN code	4061792230620
Battery voltage	18 V
Air output max.	3300 l/min / 117 cfm
Vacuum	140 hPa (mbar) / 2 psi
Filter surface	3500 cm <sup>2</sup> / 542 sq.inch
Container volume	30 l / 8 gal
Suction hose Ø	32 mm / 1 1/4 "
Hose length	3.2 m / 10.5 ft
Weight without battery pack	10.3 kg / 22.7 lbs

### Scope of delivery

Antistatic suction hose Quick (Ø 32 mm / 3.2 m), CordlessControl transmitter with fixing tape Ø 35 mm, 3 Suction tubes (chrome-plated), PE Disposal bag, Fleece filter bag, Suction nozzle (120 mm wide), Floor nozzle (360 mm wide), Crevice nozzle, Brush nozzle, Coupling bush Quick Ø 28/35 mm, Coupling bush Quick Ø 40/45 mm, Handle adapter Quick Premium, without battery pack, without charger