



SM 18 LTX BL with two sanding pads

- Compact multi sander with triangular and rectangular sanding plates for versatile sanding of corners, edges, and small surfaces
- Comfortable guidance close to the surface thanks to the low overall height.
- Low-vibration working thanks to smooth running operation
- Grip area with non-slip soft-grip surface
- Unique Metabo brushless motor highest efficiency when grinding, also in continuous mode
- Orbit diameter 2.0 mm for highest surface quality with good material removal
- Infinitely variable speed control for working with different materials
- With easy to empty textile dust bag for working without extraction facilities
- Can be connected to an all-purpose vacuum cleaner with the coupling bush 630798000
- Removable protector protects adjacent surfaces and increases the service life of the sanding plate
- With attachment point for tool safety straps for working at great heights

Order no.	602089840
EAN code	4061792252509
Battery voltage	18 V
Base plate	100 x 150 mm
No-load speed	4000 - 10000 rpm
Orbital frequency with no load	8000 - 20000 rpm
Orbit diameter	2 mm
Weight without battery pack	1.1 kg
Weight with battery pack	1.5 kg

Scope of delivery

Base plate 190x150 mm with hook and loop, Base plate 80x133 mm with hook and loop, Protector 100x150 mm, Protector 80x133 mm, 1 Hook and loop sanding sheet P 120 wood and metal "professional" (100x150 mm), 1 Hook and loop sanding sheet P 120 wood and metal "professional" (80x133 mm), Textile dust bag compact, Hexagonal wrench, metaBOX 215, without battery pack, without charger