



## SB 18 Set with 78-piece mobile workshop

- Light, compact cordless hammer drill with extremely compact design for versatile use
- Hammer drill function for drilling in masonry
- Mobile workshop (78 pieces): 5 wood drill bits (4/5/6/8/10mm), 5 masonry drill bits (5/6/7/8/10mm), 14 HSS drill bits (1.5/1.5/2/2/2.5/3/3/3.5/4/4.5/5/5.5/6/6.5mm), 20 screwdriver bits length 25mm (PH1/PH2/PH2/PH3/PZ1/PZ2/PZ2/PZ2/PZ3/H3/H4/H5/H6/T15/T20/T25/T30/S4/S5/S6), 10 screwdriver bits length 50mm (S4/S5/S6/PZ1/PZ2/PZ3/T15/T20/T25/T30), 10 screwdriver bits length 75mm (S4/S5/S6/PZ1/PZ2/PZ3/T15/T20/T25/T30), bit holder (60mm), 8 socket wrench (6/7/8/9/10/11/12/13mm), countersink (12.7mm), centering pin (5x100mm), cutter knife with 2 spare blades, measuring tape (3m/10"), pencil (HB)
- Integrated working light to illuminate the contact area
- With handy belt hook and bit case which can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no. EAN code	602245710 4061792249509
Type of battery pack	Li-Power
Battery voltage	18 V
Battery pack capacity	2 x 2 Ah
Maximum torque, soft	24 Nm / 212 in-lbs
Maximum torque, hard	48 Nm / 425 in-lbs
Adjustable torque	0.5 - 4.5 Nm // 4 - 40 in-lbs
Drill-Ø masonry	10 mm / 3/8 "
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	20 mm / 3/4 "
No-load speed	0 - 450 / 0 - 1600 rpm
Maximum impact rate	24000 bpm
Chuck capacity	1 - 10 mm // 1/32 - 3/8 "
Weight without battery pack	0.92 kg / 2 lbs
Weight with battery pack	1.3 kg / 2.9 lbs

### Scope of delivery

Keyless chuck, Belt hook and bit case, 2 Li-Power battery packs (18 V/2.0 Ah), Charger SC 30, Plastic carry case, Accessory set