



BS 18 L BL Set with 74-piece mobile workshop

- Smallest Metabo 18 volt drill/screwdriver with powerful Brushless performance for all standard drilling and screwdriving applications
- Mobile workshop (74 pieces): 5 wood drill bits (4/5/6/8/10mm), 14 HSS drill bits (1.5/1.5/2/2/2.5/3/3/3.5/4/4.5/5/5.5/6/6.5mm), 20 screwdriver bits length 25mm (PH1/PH2/PH2/PH3/PZ1/PZ2/PZ2/PZ2/PZ3/H3/H4/H5/H6/T15/T20/T25/T30/S4/S5/S6), 10 screwdriver bits length 50mm (S4/S5/S6/PZ1/PZ2/PZ3/T15/T20/T25/T30), 10 screwdriver bits length 75mm (S4/S5/S6/PZ1/PZ2/PZ3/T15/T20/T25/T30), bit holder (60mm), 8 socket wrench (6/7/8/9/10/11/12/13mm), countersinks (12.7mm), centering pin (5x100mm), cutter knife with 2 spare blades, measuring tape (3m/10"), pencil (HB), notebook
- Extremely short and light drill/screwdriver for comfortable handling also over head or in tight spaces
- Robust, durable gear housing made from aluminium die-cast
- Powerful Brushless motor for greatest efficiency and long battery pack runtime
- Overload protection: protects the motor from overheating
- Integrated LED work light with afterglow function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	613155710
EAN code	4061792254541

Type of battery pack	Li-Power
Battery voltage	18 V
Battery pack capacity	2 x 2 Ah
Maximum torque, soft	28 Nm / 247.8 in-lbs
Maximum torque, hard	65 Nm / 575.3 in-lbs
Adjustable torque	0.5 - 9 Nm // 4.4 - 79.7 in-lbs
Drill Ø steel	13 / 1/2 "
Drill-Ø soft wood	40 / 1 9/16 "
No-load speeds	0 - 500 / 0 - 1700 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	0.9 kg / 2 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, 2 Li-Power battery packs (18 V/2.0 Ah), Charger SC 30, Plastic carry case, Accessory set