



## BS 18 L BL Q

- Smallest Metabo 18 volt drill/screwdriver with powerful Brushless performance for all standard drilling and screwdriving applications
- Extremely short and light drill/screwdriver for comfortable handling also over head or in tight spaces
- Metabo Quick System: quick change of bit retainer and bits, for flexible working
- Robust, durable gear housing made from aluminium die-cast
- Spindle with magnetic hexagon recess for screwdriver bits for working without chuck
- Powerful Brushless motor for greatest efficiency and long battery pack runtime
- Overload protection: protects the motor from overheating
- Integrated LED work light with afterglow function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	613156800
EAN code	4061792245914
Type of battery pack	LiHD
Battery voltage	18 V
Battery pack capacity	2 x 4 Ah
Maximum torque, soft	28 Nm / 247.8 in-lbs
Maximum torque, hard	65 Nm / 575.3 in-lbs
Adjustable torque	0.5 - 9 Nm // 4.4 - 79.7 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	40 mm / 1 9/16 "
No-load speeds	0 - 500 / 0 - 1700 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	0.9 kg / 2 lbs
Weight with battery pack	1.5 kg / 3.2 lbs

### Scope of delivery

Quick-change chuck, Belt hook and bit case, 2 LiHD Battery packs (18 V/4.0 Ah), Charger ASC 55 "AIR COOLED", metaBOX 145