



Multifunctional table MWB 100

- Mobile workshop with many fields of application
- Fast setup and dismantling thanks to folding mechanism
- Height-adjustable feet for optimal working height
- Levelling foot to compensate uneven grounds
- Circumferential T-groove for lateral clamping with suitable clamps
- Robust MDF table top (replaceable) with 20 mm dog holes and angle display
- Several tables can be connected thanks to supplied corner connectors
- Numerous fastening options for semi-stationary tools
- Easy transport thanks to light aluminium frame and transport handles
- Circumferential groove for suspending suitable open fronted storage bins

Order no.	626991000
EAN code	4061792253582
Weight	22.1 kg / 48.7 lbs
Max. load	120 kg / 264.6 lbs
Height	800 - 1000 mm // 31 1/2 - 39 3/8 "
Material of table top	MDF
Material thickness of table top	20 mm / 25/32 "
Bore diameters	20 mm / 25/32 "
Table dimensions	710 x 960 mm // 27 15/16 x 37 13/16 "
Dimensions, set-up	750 x 1000 x 1000 mm // 29 17/32 x 39 3/8 x 39 3/8 "
Dimensions, folded	750 x 1000 x 88.5 mm // 29 17/32 x 39 3/8 x 3 1/2 "