



Combo Set 2.8.3 18V BS 18 L BL + SSD 18 LT 200 BL

- Cordless impact driver SSD 18 LT 200 BL: Compact brushless cordless impact driver with 1/4" hexagon recess and 200 Nm
- Cordless drill/screwdriver BS 18 L BL: Brushless drill/screwdriver with compact design for universal application areas


Order no.
EAN code

68519500
4061792210585


Scope of delivery

Cordless drill/screwdriver BS 18 L BL, cordless impact driver SSD 18 LT 200 BL, 1 Li-power battery pack (18 V/2.0 Ah), 1 Li-power battery pack (18 V/5.2 Ah), charger ASC 55, metaBOX 145 L

Cordless drill / screwdriver BS 18 L BL

	Battery voltage	18 V
	Maximum torque, soft	25 Nm / 221.3 in-lbs
	Maximum torque, hard	60 Nm / 531 in-lbs
	Adjustable torque	0.5 - 5 Nm // 4.4 - 44.3 in-lbs
	Drill Ø steel	13 mm / 1/2 "
	Drill-Ø soft wood	32 mm / 1 1/4 "
	No-load speeds	0 - 550 / 0 - 1850 rpm
	Chuck capacity	1.5 - 13 mm // 1/16 - 0.51181 "
	Weight without battery pack	0.87 kg / 1.9 lbs
	Weight with battery pack	1.3 kg / 2.9 lbs
		<ul style="list-style-type: none"> • Brushless drill/screwdriver with extremely compact design for universal application areas • Integrated LED work light with afterglow function for optimal brightness in the work area • With handy belt hook and bit case which can be fixed either on the right or left side • Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Cordless impact driver SSD 18 LT 200 BL

	Battery voltage	18 V
	Max. screw size	M16
	Max. no-load speed	3050 rpm
	Maximum impact rate	3750 bpm
	Maximum torque	200 Nm
	Speed/torque levels	3
	Bit retainer	Hexagon recess 1/4" (6.35 mm)
	Weight without battery pack	1.17 kg / 2.6 lbs
	Weight with battery pack	1.57 kg / 3.5 lbs
		<ul style="list-style-type: none"> • Compact cordless impact driver with 1/4" hexagon socket and 200 Nm • Unique Metabo brushless motor for quick work progress and highest efficiency for any application • Three speed/torque levels for a varied range of applications • Integrated work light for illumination of the work area • Robust die cast aluminium gear housing for optimum heat dissipation and durability • Handy belt hook, can be fixed either on the right or left side