



BS 18 LT BL

- Brushless drill/screwdriver with optimal power for demanding applications
- Powerful Brushless motor for greatest efficiency and long battery pack runtime
- Integrated working light to illuminate the contact area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602325500
EAN code	4007430326317
Type of battery pack	Li-Power
Battery voltage	18 V
Battery pack capacity	2 x 4 Ah
Maximum torque, soft	34 Nm / 301 in-lbs
Maximum torque, hard	75 Nm / 663.8 in-lbs
Adjustable torque	0.7 - 8 Nm // 6 - 71 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	38 mm / 1 1/2 "
No-load speeds	0 - 600 / 0 - 2100 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.2 kg / 2.6 lbs
Weight with battery pack	1.9 kg / 4.2 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, 2 Li-Power battery packs (18 V/4.0 Ah), Charger ASC 55 "AIR COOLED", metaBOX 145